



SCAN in a BOX

THINK OUT OF THE BOX!



AUTOMATIC TURNTABLE

M A D E I N I T A L Y

MORE THAN 15 YEARS OF EXPERIENCE AT YOUR SERVICE

Extend the potential of Scan in a Box and push the performance beyond limits. See how far you can go! The 3D Scanning has never been so easy. Try, to not regret. Connect the Automatic Turntable to unlock the new Scan Mode inside IDEA the Software. Benefit from a total efficiency thanks to the automatic Axis Alignment.

- Designed and Engineered in Italy
- Affordable Investment to Reach the Top Professional Quality
- Created specifically to benefits of IDEA The Software 1.1 toolkit
- Consent to boost the Experience of use of Scan in a Box
- Grant more Efficiency during the Workflow
- Enhance the Productivity by saving time
- More Control and Automatism with less users' effort

Make it 3D. Make it Now.

AUTOMATIC TURNTABLE - TECHNICAL SPECIFICATIONS

| | |
|--------------------------|---|
| ATT Dimensions | Ø 200 x 65 mm |
| Box Dimensions | 260 x 380 x 85 mm |
| ATT Weight | 1,8 kg |
| Box Weight | 2,6 kg |
| Object Weight | Up to 10 kg |
| Material | Aluminum |
| Operating Voltage | 24 Vdc |
| Max Operating Current | 1000 mA |
| Supply Voltage | Universal, 90~277 Vac |
| ATT Batch 3D Scan Module | Automatically unlock at the first connection |
| ATT Alignment | Automatic Axis Alignment / Manual Alignment |
| ATT Scanning Time | ≤ 4 secs per scan / ≤ 55 secs per 8 scans/360° view |

MINIMUM TECHNICAL REQUIREMENTS

| | |
|-------------------------|-----------------------------------|
| Software | IDEA the Software 1.1 or higher |
| PC and Operating System | As for Scan in a Box requirements |
| Connectivity | X1 USB 2.0 |

Scan in a Box Automatic TurnTable is an optional accessory, sold separately. It requires Scan in a Box base kit to run.



Take full advantage of Scan in a Box by combining the Automatic TurnTable with the already well-proven IDEA the Software (since version 1.1). You can keep working by strategically move the scan object or you can place it on the round plate and make **multiple acquisitions** with just a click.

Maintain the default settings to get no. 8 sequential scans in a 360° rotation of the ATT in less than 55 secs or setup your custom parameters by setting up the number of acquisitions and the rotation angle range as you like. In few minutes you will get the scans' group **auto aligned** and ready to start over again: the **Axis Alignment** will be performed automatically.

Every scanning result is always completely compatible with another.

Switch from 3D Scan free mode to Multiple Scan Mode with ATT and viceversa as needed!



Become part of our distribution network

SCAN IN A BOX
www.scaninabox.com
contacts@scaninabox.com

OPEN TECHNOLOGIES SRL
Via Matteotti, 161-163 A - 25086 Rezzato (BS) - ITALY
Ph.: +39 030 3543106 - Fax.: +39 030 349451
VAT ID. IT03598170177